

# ACCU-PULSE III

## Pulsation Dampeners

Chargeable / Metal / Dome Top



- remove pulsating flows from positive displacement pumps
- increase system efficiency and pump life
- decrease maintenance and costs
- protect pipes, meters, instruments, valves, gaskets and seals from pulsation and vibration
- ensure meter accuracy, longevity and repeatability
- reduce pressure fluctuations and diaphragm wear
- prevent foaming and splashing

### FEATURES

- CRN is available on certain metallic units
- extensive range of materials
- lightweight, compact design
- 1000 psi rating
- easy in-line maintenance
- 2 year warranty

### Technical Data

**Unit Capacity:** 370 CU In

**Weight:** 37-40 pounds

**Air Control:** Gas Fill Valve

**Inlet Port:** 2" NPTF

**Pressure Limit:** 1000 psi at 70° F \*\*

**Shell Materials:** 316L Stainless Steel, Alloy 20, Hastelloy C, Carbon Steel

**Elastomers:** Neoprene, Buna-N, EPDM, Viton, Hypalon

*\*\*Caution: Temperature and pressure affect the strength and chemical resistance of plastic and rubber.*



PRIMARY FLUID  
SYSTEMS INC.

Call Toll Free 1-800-776-6580


Tel (905) 333-8743 Fax (905) 333-8746

E-Mail: primary@primaryfluid.com  
<http://www.primaryfluid.com>


### Operation:

ACCU-Pulse pulsation dampeners operate on the principle that volume is inversely proportional to pressure. Compressed air or gas is introduced into the top section of ACCU-Pulse to a specified pressure that must be lower than the pump's discharge pressure. When a pump or valve introduces a pulse, fluid enters the dampener and compresses the trapped gas. The fluid remains in the dampener until the system pressure returns to normal, when the valve is reopened or the pump begins its next cycle. The fluid is then pushed back into the system piping as the trapped gas expands. ACCU-Pulse does NOT restrict fluid flow, or increase system pressure. ACCU-Pulse fills the fluid voids and pressure fluctuations created by reciprocating pumps.

### Typical Installations:




### Dimensions:



### Parts Description:

Item	Part #	Qty	Description	Material
1	901-28	1	Wetted Housing	Stainless Steel
	907-28		Wetted Housing	Alloy 20
	905-28		Wetted Housing	Hastelloy C
◊ 2	105-25	1	Bladder with anti-extrusion button	Neoprene
	205-28		Bladder with anti-extrusion button	EPDM
	205-29		Bladder with anti-extrusion button	Buna - N
	205-30		Bladder with anti-extrusion button	Hypalon
	205-25		Bladder with anti-extrusion button	Viton
	105-55		Bladder with anti-extrusion button	Aflas
3A	901-24	1	NonWetted Housing	316 Stainless Steel
◊ 4	G32	1	Gauge ( Elastomer Bladders )	S/S / Brass
◊ 5	102-70	1	Fill Valve	Stainless Steel
6	921-47	8	Fastener Assembly	Stainless Steel
			For alloy, hastelloy units consult factory for bladders	
◊ Recommended Spare Parts				

Distributed by:



Call Toll Free 1-800-776-6580

Tel: (905) 333-8743

Fax: (905) 333-8746

E-Mail: [primary@primaryfluid.com](mailto:primary@primaryfluid.com)  
<http://www.primaryfluid.com>

Distribution Territories Available

© Registered Trade Mark of Primary Fluid Systems

