ACCU-PULSE II Pulsation Dampeners

Chargeable / Plastic / Dome Top



- remove pulsating flows from positive displacement pumps
- · increase system efficiency and pump life
- decrease maintenance and costs
- protect pipes, meters, instruments, valves, gaskets and seals from pulsation and vibration
- ensure meter accuracy, longevity and repeatability
- reduce pressure fluctuations and diaphragm wear
- prevent foaming and splashing

FEATURES

- · lightweight, compact design
- 150 psi rating
- extensive range of materials

- easy in-line maintenance
- 2 year warranty

Technical Data

Unit Capacity: 85 CU In Weight: 6-7 pounds

Air Control: Gas Fill Valve

Inlet Port: 3/4" NPTF, optional 1" NPTF

Pressure Limit: 150 psi at 70° F **

Shell Materials: Polypropylene, PVC, PVDF

Elastomers: Neoprene, Buna-N, EPDM, Viton, Hypalon, Teflon

**Caution: Temperature and pressure affect the strength and chemical resistance of plastic and rubber.




ACCU-PULSE II Pulsation Dampeners


Operation:

ACCU-Pulse pulsation dampeners operate on the principal that volume is inversely proportional to pressure. Compressed air or gas is introduced into the top section of ACCU-Pulse to a specified pressure that must be lower than the pump's discharge pressure. When a pump or valve introduces a pulse, fluid enters the dampener and compresses the trapped gas. The fluid remains in the dampener until the system pressure returns to normal, when the valve is reopened or the pump begins its next cycle. The fluid is then pushed back into the system piping as the trapped gas expands. ACCU-Pulse does NOT restrict fluid flow, or increase system pressure. ACCU-Pulse fills the fluid voids and pressure fluctuations created by reciprocating pumps.

Typical Installations:



Dimensions:



Parts Description:

Ite m	Part#	Qty	Description	Material
1	*311-27-^	1	Wetted Housing	PVC
	*301-27-^		Wetted Housing	GF Polypropylene
	*401-27-^		Wetted Housing	PVDF
+ 2	301-25	1	Bladder	Neoprene
	401-28		Bladder	EPDM
	401-29		Bladder	Buna-N
	401-30		Bladder	Hypalon
	401-25		Bladder	Viton
	301-55		Bladder	Aflas
	301-10		Bladder	Teflon
3A	*311-24	1	NonWetted Housing	PVC
	*301-24		NonWetted Housing	GF Polypropylene
4	103-51	1	Ring Band Assy	GF Noryl
+ 5	101-33	1	Gauge	Plastic / Brass
+ 6	101-70	1	Fill Valve	Brass
^ add suffix -2 for units with 3/4" connections				
^ add suffix -3 for units with 1" connections				
* add suffix T for Wetted & NonWetted Housing withTeflon Bladders				
Recommended Spare Parts				

Distributed by:



Call Toll Free 1-800-776-6580

Tel: (905) 333-8743 Fax: (905) 333-8746

E:Mail: primary@primaryfluid.com http://www.primaryfluid.com